

Micro Nano Mill

The Micro Nano Mill is the most efficient media mill in the world for nano grinding solids in liquids! For the first time in a laboratory environment, small batches can be 99% recovered. The mill chamber self-discharges feedstock, eliminating waste and simplifying clean up.

Standard Features

- ❖ 2 HP Motor, Non XP, 460V, 3 Phase at 60 hz
- ❖ 0-9000 rpm, infinitely adjustable electronics ensures constant speed even with viscosity changes
- ❖ Digital display shows readout of speed with timer adjustable to 999 minutes
- ❖ Mixing element and shaft constructed of stainless steel
- ❖ Adjustable quick fit clamping device
- ❖ Electronic safety switch, including a motor protective switch that prevents starting the machine when there is no vessel in place and when the mill head is not lowered into the vessel
- ❖ 1 ½ liter holding, 750 ml working, type 304 stainless steel process level

Options

- ❖ 2 Liter holding, 1 liter minimum, 1 ½ liter maximum working capacity, type 304 stainless steel process vessel
- ❖ High speed mixing shaft assembly permits use of machine as a disperser
- ❖ High speed rotor-stator assembly permits use of machine as a rotor-stator



HOCKMEYER

Visit us at www.hockmeyer.com.